



## PRODUCT DATA SHEET

# TSW-5 Spray Clean™

Initially formulated to aid in the removal of latex acrylic paint from spray equipment during the cleanup operation. Add to water to rinse hoses, pumps and spray mechanisms. It dissolves deposits of dried paint that hide in small crevices and on surfaces where the paint has been in contact.

Also use in diluted form to thoroughly clean brushes, rollers and more (Developed for latex not oil). To clean dried paint longer soaking time may be required.

**Directions for internally cleaning sprayer:** For cleanup after each job, add 4 ounces Spray Clean to 3 gallons of fresh water. Run the solution through the entire apparatus following the same procedure as when painting. The final few ounces of water should be clear. If there is still paint residue in the water, repeat process. Do not store in spray rig.

**Directions for cleaning brushes & rollers:** To thoroughly clean brushes and rollers after using latex or acrylic paints or TSW4 Acryli-Master, mix three parts water to one part TSW5 Spray Clean. You will get multiple cleanings out of this mixture. To remove dried or hardened paint you will need to soak the brushes or rollers for an extended period of time.

**Directions for cleaning spray equipment parts:** To thoroughly clean parts that are covered with hardened paint, mix 8 ounces of TSW5 Spray Clean to ½ gallon of water. Soak the parts until the paint has softened and loosened from the surfaces. Use a pick for removal from areas that are thickly coated.

**Health & Safety:** Chemical resistant rubber gloves are recommended for unprotected hands during mixing or use. Guard against splashing in eyes. Avoid sprayed mists. Product is irritating to unprotected skin and is extremely irritating to eyes. **First Aid:** For skin contact, flush with large amounts of water. For eye contact, flush with water for at least fifteen minutes. If irritation persists, contact a physician. Use of this product causes no known health effects.

Phone: 800-447-2334 / 800-4graffiti / Fax – 925-443-5209 /

[www.TSWwarehouse.com](http://www.TSWwarehouse.com)